

Pro Truing stand 2.1

1689 2.1

NEU



Produkteigenschaften

- Die Geometrie des Prüffühlers ermöglicht auch die gleichzeitige axiale Kontrolle der Zentrierung des Rades.
- The upright arms position can be adjusted with an upright adjustment knob to fit the axle width.
- The caliper arm position can be adjusted to fit the wheel radius and the caliper tip distance can be adjusted to fit the rim width.
- Spring loaded caliper arm and the calipers can be quickly pulled away, automatically springing back to a set position when inserting a new wheel. This enables faster work of several same size wheels.
- Strong base for high precision Longer and redesigned upright arms for increased clearance and truing accuracy
- Wide calipers for greater wheel clearance

- Supports through axle hubs up to 197 mm width (with use of adapters). Max. arm opening 230 mm (without adapters)
- Neue Lager an der Einstellachse des aufrechten Arms sind federgespannt, um die Präzision zu verbessern und die Häufigkeit der Kalibrierung zu verringern
- Composite caliper tips prevent scratching the rim and are designed to make radial truing easier
- Precision threads and springs for smooth operation 8 mm bench mount holes at the bottom, 268 mm center to center
- Clean, all-black design
- Includes conical magnetic through axle adapters, one size fits all (12, 15 and 20). Adapters can be affixed anywhere on the base and secured to the upright arms with a bolt for a more permanent setup.
- Includes white high gloss stickers for the base and caliper arm, improving background contrast (stickers are not preapplied)

Kompatibilität:

- Accepts wheels up to 32" with tire installed
- Das System ist kompatibel mit Festklemm-, Schnellklemm- und Hohlachsspannern.
- Zum Zentrieren von Felgen mit Naben mit Hohlachsen müssen Adapter verwendet werden (im Lieferumfang enthalten).
- Ein Paar Hohlachsadapter ist für alle Hohlachsmaße geeignet.

								
640434	390	40	40	226	525	298	342	8550

* Bilder von Produkten sind Symbolfotos. Abmessungen sind in mm, Gewichte in Gramm.

Verwendung (Bilder)

